



F&J SPECIALTY PRODUCTS, INC.

PO Box 2888

Ocala, Florida 34478-2888

Tel: (352) 680-1177 • (352) 680-1178

Fax: (352) 680-1454

Email: fandj@fjspecialty.com Internet: www.fjspecialty.com

The Nucleus of Quality Air Monitoring Programs

Carbon 14 Collection System Model MRB200C14E

NOTABLE FEATURES:

- Inorganic CO₂ in Air Collection System
- Automatic Flow Control
- Digital Flowmeter displaying flow, elapsed time and accumulated volume
- Large, bright LED Display
- Correction of flow rate and volume to a reference temperature and pressure (4 options)
- Tri-20ml bubbler system
- 220-240VAC; 50/60Hz; single phase



GENERAL DESCRIPTION:

The Model MRB200C14E C-14 collection system consists of a three 20 ml vial bubbler train for collection of inorganic carbon species in air. A diaphragm pump with an automatic flow control mechanism utilizing the F&J digital flowmeter system is provided.

Typical flow range is 75 to 200 sccm.

Real-time data download is available through the RS232 port. An optional flash card data storage device is available.

The unit is designed for periodic indoor use. Please consult the product specifications for the design temperature range and the installation category.

Collection efficiency for inorganic C-14 in air is greater than 99% utilizing ethanolamine.

Rev.: 16 September 2019

MRB200C14E C-14 Collection System (220 – 240VAC)

SPECIFICATIONS:

PUMP TYPE:	Diaphragm
MOTOR:	Brushless Type
MAXIMUM CAPACITY:	Typical 75 cc/min to 200 cc/min. control range
POWER REQUIREMENTS:	220 - 240 VAC; 50 Hz; 1 ampere; single phase
CIRCUIT BREAKER PROTECTION:	5 amperes
ELECTRICAL CORD:	All temperature, 3-wire, 16 gauge
DIMENSIONS:	14”H × 9”W × 12.5”D (35,6 cm H × 22,9 cm W × 31,8 cm D)
WEIGHT:	17.5 lbs. (8 kg)
INSTALLATION CATEGORY:	Pollution Degree 2

C-14 COLLECTION SYSTEM:

- Removable 20 ml scintillation vials; One three vial train
- Detection Limit: 1E-10 μ Ci/cc
- Efficiency: > 99% with ethanolamine

AIR FLOW MEASUREMENT SYSTEM

- Air flow: \pm 4% of full scale
- Temperature: \pm 0.9°F (0.5°C) (Not displayed)
- Absolute Pressure: \pm 0.6 inches Hg (15,24 mm Hg) (Not displayed)

ON-BOARD CALCULATIONS

- Flow calculation from differential pressure value corrected to a reference T and P
- Elapsed Time
- Cumulative Volume corrected to a reference T and P

OPERATING TEMPERATURE: (0° to 40°C) (32°F to 104°F)

STORAGE TEMPERATURE: (-10°C to 50°C) (14°F to 122°F)

OPERATING HUMIDITY: 0-95% RH non-condensing

COMMUNICATIONS INTERFACES: RS-232 available for real-time data download of airflow data

OPTIONS:

- Flash Card Data Storage Device 232FCDS
- Flash Card (2 GB) 372239
- PC Flash Card Reader SDDR-199-A20